

Yale

Electronic Safes L2

Yale Electronic Safes L2 provide you with a basic level of security for those items you need more regularly, such as keys, passports, cash and cards.

Each safe is accessed via an easy to set three to eight digit PIN. Two keys are also supplied, in case of a forgotten PIN.

The safe features a two-stage lockdown mechanism. It first activates for 20 seconds if an incorrect PIN is entered three times. If three more incorrect PIN entries occur, the lockdown extends to 5 minutes. The lockdown can be stopped by using a key to open the safe.

The safes come in a variety of sizes from mini to laptop variants, allowing you to choose a safe that best suits your needs.

A basic level of security suitable for:



Important Documents



Passports



Smart Devices



Keys



Laptop



Camera

- Electronic lock with handle for easy opening
- 3 to 8 digit PIN code access
- Automatic lockdown: The keypad locks down for 20 seconds after three incorrect PIN entries. After three more incorrect PIN entries, it locks down for 5 minutes
- Easy one-touch PIN reset button inside the safe
- Locking mechanism: Mini Motor
- Mechanical override - two radial keys supplied to open the safe in case of a forgotten PIN
- Simple LED light status indicators
- Silent mode option when entering the PIN code or when the safe is opening

Trusted every day



Specifications

Access credentials	PIN code
Keypad	Three to eight digit PIN code access
Locking bolts	Two 16mm bolts
Locking mechanism	Mini Motor
Automatic lockdown	The keypad locks down for 20 seconds after three incorrect PIN entries. After three more incorrect PIN entries, it locks down for 5 minutes.
Key Back-Up	Two radial keys
Silent input	Switch sound off for PIN code entry and safe opening
Batteries	Inside the safe (4x AA)
Status indicators	LED light indicators
PIN code reset	Easy one-touch PIN reset button inside the safe



Mini



Small



Laptop



Medium



Large

Product code	YSV/170/DB3	YSV/200/DB3	YLV/200/DB3	YSV/250/DB3	YSV/390/DB3
Exterior dimensions	H170xW230xD170mm	H200xW310xD200mm	H200xW430xD350mm	H250xW350xD250mm	H390xW350xD360mm
Interior dimensions	H165xW225xD130mm	H195xW305xD150mm	H195xW425xD300mm	H245xW345xD200mm	H385xW345xD305mm
Door clearance	H125xW145mm	H145xW245mm	H145xW365mm	H195xW285mm	H325xW275mm
Net weight	2.8kg	4kg	7.7kg	5.8kg	12.5kg
Volume	4.8 litres	8.6 litres	24 litres	16.3 litres	40 litres
Colour availability	Black, Blue and Pink	Black	Black	Black	Black