



**Part Number :** [334724104](#)

**Product Description :** MX150 Mat-Sealed Female Connector Assembly, Dual Row, 4 Circuits, Keying Option D, without Connector Position Assurance, with Open Lengthened Grommet Cap, Stone Gray

**Series Number :** 33472

**Status :** Active

**Product Category :** Connector Housings



---

## Documents & Resources

### Drawings

[334724104 sd.pdf](#)

[PK-31300-903-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-33472-100-001.pdf](#)

[AS-33472-100-CH-001.pdf](#)

[AS-33472-100-FR-001.pdf](#)


[AS-33611-001-001.pdf](#)

[PS-33472-000-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane;

	Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 4 Circuits, Keying Option D, without Connector Position Assurance, with Open Lengthened Grommet Cap, Stone Gray
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	889056506731

### Agency

UL	E29179
----	--------

## Physical

Circuits (maximum)	4
Color - Resin	Stone Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	8.180/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Male Connector Assemblies	<u>33482</u>

### Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>