

## Monitorarm

### 00095826 FULLMOTION Monitor Arm, 66 cm (26"), 1 arm, black



**Highlightstext:**

- For installing TFT/LCD/LED monitors with a screen size from 25 to 66 cm (10" to 26")
- Easy fix system for easy and continuous adjustment of the screen
- The retaining system keeps your workplace tidy and allows you to work ergonomically
- 360° rotation for horizontal or vertical orientation of the TV
- Cable manager provides organisation and necessary strain relief
- Continuously height-adjustable on the holding rod (max. total height: 38.5 cm)
- Compatible for screens up to VESA 100x100
- +85°/-90° continuous tilt
- Extendible up to max. 12.7 cm
- Can be swivelled up to 360°
- Integrated cable routing
- Can be fixed to a table by means of a clamping screw (tabletop thickness: max. 9.5 cm)

**Technical Details:**

- Maximum Load: 10 kg
- Model: Monitor Arm
- Monitor Fixation Standard: VESA incl. Adapter Plate
- Rotation Range: 360 °
- Tilt +/-: 85 / 90 °
- Adjustable Distance: Yes
- Max. Monitor Size: 66 cm
- VESA Standard: 100 x 100 mm/75 x 75 mm
- Width x Depth x Height: 11,5 x 17,3 x 50,8 cm
- Colour: Black
- For Monitors: 66 cm
- For a Table Top Thickness of: 9.5 cm

**Scope Of Delivery:**

- 1 FULLMOTION monitor arm
- Mounting hardware
- Mounting instructions

	<b>Brand</b>	<b>Item-no.</b>	<b>VE</b>
	<b>hama</b> <sup>®</sup>	00095826	8