



OUR OFFER

SIEMENS – SINAMICS G120C

G120C Inverter Drives

The perfect balance of performance, simplicity and cost-efficiency

Inverter Drives Without Filter - 3-Phase - 380-480V

Stock-No.	Siemens MPN	Power Rate	Communication Interface
791-8591	6SL3210-1KE11-8UB1	0.55 kW	USS, Modbus RTU
791-8605	6SL3210-1KE12-3UB1	0.75 kW	USS, Modbus RTU
791-8602	6SL3210-1KE13-2UB1	1.1 kW	USS, Modbus RTU
791-8614	6SL3210-1KE14-3UB1	1.5 kW	USS, Modbus RTU
791-8627	6SL3210-1KE15-8UB1	2.2 kW	USS, Modbus RTU
791-8624	6SL3210-1KE17-5UB1	3 kW	USS, Modbus RTU
791-8636	6SL3210-1KE18-8UB1	4 kW	USS, Modbus RTU
791-8649	6SL3210-1KE21-3UB1	5.5 kW	USS, Modbus RTU
791-8646	6SL3210-1KE21-7UB1	7.5 kW	USS, Modbus RTU
791-8655	6SL3210-1KE22-6UB1	11 kW	USS, Modbus RTU
791-8658	6SL3210-1KE23-2UB1	15 kW	USS, Modbus RTU
791-8652	6SL3210-1KE23-8UB1	18.5 kW	USS, Modbus RTU

Inverter Drives With Filter - 3-Phase - 380-480V

Stock-No.	Siemens MPN	Power Rate	Communication Interface
791-8598	6SL3210-1KE11-8AB1	0.55 kW	USS, Modbus RTU
883-8733	6SL3210-1KE11-8AP1	0.55 kW	PROFIBUS DP
883-8730	6SL3210-1KE11-8AF1	0.55 kW	PROFINET, EtherNet/IP
791-8595	6SL3210-1KE12-3AB1	0.75 kW	USS, Modbus RTU
744-9584	6SL3210-1KE12-3AP1	0.75 kW	PROFIBUS DP
883-8721	6SL3210-1KE12-3AF1	0.75 kW	PROFINET, EtherNet/IP
791-8608	6SL3210-1KE13-2AB1	1.1 kW	USS, Modbus RTU
883-8752	6SL3210-1KE13-2AP1	1.1 kW	PROFIBUS DP
883-8774	6SL3210-1KE13-2AF1	1.1 kW	PROFINET, EtherNet/IP
791-8611	6SL3210-1KE14-3AB1	1.5 kW	USS, Modbus RTU
883-8777	6SL3210-1KE14-3AP1	1.5 kW	PROFIBUS DP
883-8761	6SL3210-1KE14-3AF1	1.5 kW	PROFINET, EtherNet/IP
791-8618	6SL3210-1KE15-8AB1	2.2 kW	USS, Modbus RTU
883-8737	6SL3210-1KE15-8AP1	2.2 kW	PROFIBUS DP
883-8771	6SL3210-1KE15-8AF1	2.2 kW	PROFINET, EtherNet/IP
791-8620	6SL3210-1KE17-5AB1	3.0 kW	USS, Modbus RTU
883-8783	6SL3210-1KE17-5AP1	3.0 kW	PROFIBUS DP
883-8780	6SL3210-1KE17-5AF1	3.0 kW	PROFINET, EtherNet/IP
791-8633	6SL3210-1KE18-8AB1	4.0 kW	USS, Modbus RTU
883-8743	6SL3210-1KE18-8AP1	4.0 kW	PROFIBUS DP
883-8749	6SL3210-1KE18-8AF1	4.0 kW	PROFINET, EtherNet/IP
791-8630	6SL3210-1KE21-3AB1	5.5 kW	USS, Modbus RTU
744-9590	6SL3210-1KE21-3AP1	5.5 kW	PROFIBUS DP
883-8746	6SL3210-1KE21-3AF1	5.5 kW	PROFINET, EtherNet/IP
883-8787	6SL3210-1KE21-7AB1	7.5 kW	USS, Modbus RTU
744-9604	6SL3210-1KE21-7AP1	7.5 kW	PROFIBUS DP
883-8799	6SL3210-1KE21-7AF1	7.5 kW	PROFINET, EtherNet/IP
883-8796	6SL3210-1KE22-6AB1	11.0 kW	USS, Modbus RTU
791-8670	6SL3210-1KE22-6AP1	11.0 kW	PROFIBUS DP
883-8803	6SL3210-1KE22-6AF1	11.0 kW	PROFINET, EtherNet/IP
883-8793	6SL3210-1KE23-2AB1	15.0 kW	USS, Modbus RTU
883-8806	6SL3210-1KE23-2AP1	15.0 kW	PROFIBUS DP
883-8800	6SL3210-1KE23-2AF1	15.0 kW	PROFINET, EtherNet/IP
883-8812	6SL3210-1KE23-8AB1	18.5 kW	USS, Modbus RTU
744-9601	6SL3210-1KE23-8AP1	18.5 kW	PROFIBUS DP
883-8765	6SL3210-1KE23-8AF1	18.5 kW	PROFINET, EtherNet/IP

Accessories

Stock-No.	Siemens MPN	Description
744-9626	6SL3255-0AA00-4CA1	BOP-2 - Basic Operator Panel BOP-2
744-9629	6SL3255-0AA00-4JA1	IOP - Intelligent Operator Panel
744-9610	6SL3097-4CA00-0YG0	Manual Documentation on DVD



For more technical information please visit:

www.rs-online.com