

PP-V4-OUT-HIFF-P-BL, empty



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 845 1560
Specification	PP-V4-OUT-HIFF-P-BL, empty
HARTING eCatalogue	https://harting.com/09458451560

Identification

Category	Accessories
Series	HARTING PushPull (V4)
Type of accessory	Outlet
Description of the accessory	Junction box empty for fixture of 2x RJ45 female inserts

Version

Fixing	Wall mounting
Details	Please order insert separately.
Pack contents	2-port outlet housing with protection caps Cable management Cable gland Label Assembly instructions

Technical characteristics

Limiting temperature	-20 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	6 ... 9 mm

Material properties

Material (hood/housing)	Polycarbonate (PC) Fibre-glass reinforced
Colour (hood/housing)	Black



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
GTIN	5713140235809
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400