



TECHNICAL DATA

OSZYJUICE® SW-6: SELECT METALS DEGREASING SOLUTION

SW-6 Select Metals Ozzyjuice® Degreasing Solution is a unique mixture of pH neutral emulsifiers and surfactants containing no solvents. The SW-6 Ozzyjuice® solution is specifically formulated to be easily rinsed from metal surfaces without streaking. Plus it is not corrosive to a wide range of yellow and ferrous metals, such as copper cobalt, silver, magnesium, nickel, aluminum, titanium, cadmium, iron and steel.



FEATURES & BENEFITS:

- NSF A1 approved (161319)
- Bioremediating
- pH neutral
- Water based
- Non-hazardous, non-flammable
- Non-toxic, non-irritating
- Less expensive to use than solvent unit
- Reduces compliance
- MIL spec: Mil-PRF-29602A

APPLICATIONS:

Specialised for aerospace, weapons or select metals

DIRECTIONS:

Add as supplied to the SmartWasher® as needed. Light comes on when the Smartwasher is low on Ozzyjuice®, see Operating manual for further instructions. Do not store below 0°C. Dispose of contents and container in accordance with local, regional, national and EU regulations.

TYPICAL PRODUCT DATA

20 Litre Pail:	1032078
NSF A1:	161319
Appearance:	Clear liquid
Evaporation Rate:	Very slow
Flash Point:	None
pH:	7.0 - 8.0
Plastic Safe:	Yes
Specific Gravity:	1.02
VOC %:	1.7
Optimal Working Temp (°C):	40 - 46 °C

OSZYJUICE DEGREASING/ CLEANING SOLUTIONS

Crude Oil:	Good
Hydraulic Trans. Fluid:	Excellent
Motor Oil:	Excellent
Solder & Flux:	Good
Bearing Grease:	Good
Automotive Grease:	Excellent
Resin Products:	Excellent
Fifth Wheel Grease:	Good
Creosote:	Good
Impacted Grease:	Good
Animal Fat:	Fair
Automotive Varnish:	Good
Burned-On Carbon:	Good
Cutting Oils:	Good
Ink/Toner:	Good
Asphalt:	Fair



Version Number: 2 Date of Issue: 28/04/2022 Date of Update: 29/10/2025



CRC INDUSTRIES EUROPE BV
 smartwashereurope.com
 SmartWasherEU@crcind.com
 SWtechsupport.emeia@crcind.com



SCAN HERE FOR
MORE INFO:

