

Mechanical Pressure > Low Pressure Gauges > 611.10

## Low Pressure Gauges - Black steel case, Brass wetted parts

### Standard features

- |  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• <b>Case:</b> Black-painted steel</li> <li>• <b>Wetted parts:</b> Copper alloy</li> <li>• <b>Window:</b> Snap-in acrylic</li> <li>• <b>Window ring:</b> None</li> <li>• <b>Dial:</b> White aluminum</li> </ul> | <ul style="list-style-type: none"> <li>• <b>Color:</b> Black aluminum</li> <li>• <b>Case fill:</b> Not available</li> <li>• <b>Accuracy:</b> ±1.5% of span</li> <li>• <b>External zero adjustment screw on dial</b></li> <li>• <b>Datasheet:</b> 611.10</li> </ul> |
|--|--|

Type		611.10	
Size		2½"	
Connection		LM	CBM
Conn. size		¼" NPT	
" H <sub>2</sub> O	mm H <sub>2</sub> O		
30 Vac	760	<b>9852344</b>	9851852
60 Vac	1500	<b>9748321</b>	9748339
100 Vac	2500	<b>9747473</b>	<b>9747465</b>
" H <sub>2</sub> O	mm H <sub>2</sub> O		
10	250	50761846	50761871
15	380	<b>9851682</b>	<b>9851860</b>
30	760	<b>9851690</b>	<b>9855785</b>
60	1500	<b>9851704</b>	9803432
100	2500	<b>9851810</b>	9851879
200	5000	<b>9851828</b>	9851887
oz./sq. in.	mm H <sub>2</sub> O		
10	440	<b>9851771</b>	
15	660	<b>9851780</b>	
20	880	<b>9851798</b>	
30	1320	<b>9851747</b>	9851917
35	1540	<b>9851801</b>	<b>9852723</b>
60	2640	<b>9851755</b>	9803548
oz./sq. in.	" H <sub>2</sub> O		
20	34	<b>9851720</b>	<b>9857281</b>
32	55	<b>9851739</b>	9855793
3 psi		<b>9851925</b>	<b>9851836</b>
5 psi		<b>9851933</b>	<b>9851844</b>
10 psi		<b>4204212</b>	<b>4204221</b>



Factory stocked items shown in **bold print**.

Items without part numbers are available. Minimum order quantities may apply - consult factory.

Reference page 79 for 611.10 options.