Professional Extension Cable VQ 2100 IP 44, 25 m red H07BQ-F 3G1,5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use IP 44.







MADE IN GERMANY | 5 YEARS MANUFACTURER GUARANTEE | DGUV-I 203-006 K2 | SPECIAL ROBUST | IP 44

Product number	9161250210
EAN	4007123687831

DESCRIPTION

- The BREMAXX® PUR cable (BQ cable) is extremely abrasion-resistant, roll-over resistant and has extreme cut and tear resistance. It is also resistant to acids and oils, weathering and microbes. Cold-resistant down to -40 °C.
- Sheath made of polyurethane.
- With extra robust earthing contact plug and coupling with sealing cap.
- UV-resistant plug and coupling with kink protection and cable seal.
- Category 2 equipment (K2 DGUV 203-005): For use in harsh operating conditions with high mechanical, physical and chemical impacts.

TECHNICAL DATA

Cable quality	PUR (polyurethane)	**Connection**	Earthed plug/Earthed coupling
Cable length	25 m	**Plug system plug**	Type E and F (Protective contact with earth hole)
Cable designation	H07BQ-F 3G1,5	**Plug system socket/ coupling**	Type F (Protective contact)
Cable colour	red	**Degree of protection (IP)**	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	**Weight of product (including packaging)**	2.68 kg
Weight of product (without packaging)	2.68 kg	**Dimension LxWxH (incl. packing)**	23 cm x 23 cm x 8 cm
Dimension LxWxH (without packing)	23 cm x 23 cm x 8 cm		

SCOPE OF DELIVERY

Professional Extension Cable VQ 2100