

12U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

Product ID: 4POSTRACK12U



The 4POSTRACK12U 12U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 12U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

Features

- 12U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

Hardware	Warranty	2 Years
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	4-Post
	Special Features	Adjustable Mounting Rails
		Base Plate with Floor-Anchoring Holes
		Built-in Cable Management
		Casters (Included)
Easy Assembly		
Grounding Lug(s)		
	Leveling Feet	
	U-Markings	
	U Height	12U
	Wallmountable	No
Performance	Weight Capacity (Stationary)	1202.9 lb [544.3 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
	Maximum Mounting Depth	40 in [101.7 cm]
	Minimum Mounting Depth	22 in [56 cm]
	Product Height with Casters	28 in [71 cm]
Product Measurements	Product Height	25.1 in [63.8 cm]
	Product Length	23.2 in [59 cm]
	Product Width	23.6 in [60 cm]
	Weight of Product	50.3 lb [22.7 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Package Height	6.3 in [16 cm]
	Package Length	25.6 in [65 cm]
	Package Width	14.2 in [36.1 cm]

	Shipping (Package) Weight	58.2 lb [26.3 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 2 - Left Vertical Rail 2 - Right Vertical Rail 2 - Base Bracket 8 - Corner Section 4 - Center Section 2 - Top Bracket 48 - M8 Bolt 48 - M8 Washer 1 - M8 (13mm) Wrench 1 - M6 (10mm) Wrench 1 - Phillips Screwdriver 24 - M6 Cage Nut 24 - PVC Cup Washer 24 - M6 Phillips Head Screw 4 - Cable Management Hook 4 - Hook Mounting Screw 4 - Casters 4 - Leveling Feet 16 - M6 Screw 16 - M6 Flat Washer 16 - M6 Flange Nut 4 - Grounding Wires

Product appearance and specifications are subject to change without notice.