



verso adjustable height workstand with 3 drawer cabinet. Featuring a robust steel channel, adjustable height framework with 30mm lino worktop. Cabinet size - WxDxH: 525x550x450mm. Drawer configuration: 3x 125mm with 100% extension slides (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 5010 gentian blue. WxDxH: 700x600x780-930mm.

Breite [mm]: 700
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 64.25
EAN-Code: 5039350033036
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Gentian blue
Main RAL colour	RAL 5010
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	3
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125
Drawer height 2 [mm]	125
Drawer height 3 [mm]	125

Schrank, Gehäuse, Werkbank und EAP

Height adjustment range [mm]	780-930
Worktop/housing top type	Lino