



# one-way flow control valve GRLA-3/8-QS-6-RS-D

Part number: 534341

★ Core product range

FESTO



## Data sheet

Feature	Value
Valve function	One-way flow control function
Pneumatic connection, port 1	QS-6
Pneumatic connection, port 2	G3/8
Adjusting element	Knurled screw
Mounting type	Threaded with external (male) thread
Standard nominal flow rate in flow control direction	495 l/min
Standard nominal flow rate in non-return direction	320 ... 495 l/min
Operating pressure	0.2 ... 10 bar
Ambient temperature	-10 ... 60 °C
Assembly position	Any
Operating pressure complete temperature range	0.2 ... 10 bar
Standard flow rate in direction of flow control: 6 -> 0 bar	740 l/min
Standard flow rate in blocked direction: 6 -> 0 bar	840 ... 890 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Storage temperature	-10 ... 40 °C
Medium temperature	-10 ... 60 °C
Maritime classification	see certificate
Nominal tightening torque	10 Nm
Product weight	72 g
Materials note	Conforms to RoHS
Material seals	NBR
Material hollow bolt	Wrought Aluminium alloy Anodised
Material release ring	POM
Material knurled head	Wrought Aluminium alloy Anodised
Material adjusting screw	High alloy steel, non-corrosive
Material swivel fitting	Zinc die-casting