

Bourdon Tube Pressure Gauges, Stainless Steel

Modelcode type: 23X.50

Item number: 63405849

Description

Design	EN 837-1
Nominal size	100 mm
Accuracy class	class 1.0
Scale range	0...40 MPa
Unit of outer Scale	MPa
2nd Scale or Special Scale	2nd scale psi
Process connection	1/2 NPT
Connector location	lower mount

Materials

Measuring system	stainless steel
Movement	
Dial	Aluminum, white
Pointer	aluminium, black
Case material	Stainless steel 1.4301
Window	laminated safety glass
Bezel ring	cam ring (bayonet type), stainless steel
Case filling fluid	glycerine

Operating conditions

Permissible medium temperature	+ 100 °C
Permissible ambient temperature	-20 ... +60 °C
Ingress protection	IP 65

Labelcode

Label	WIKA standard without / with Tag-number
language of the label	German

