


























Cordless: Battery / Charger Reference Chart

		Charger	DC1414	DC1439	DC1804	DC245A	DC705A	DC10WA	DC18RA	DC36RA
			7.2V 12V 9.6V 14.4V	7.2V 12V 9.6V 14.4V	7.2V 14.4V 9.6V 18V 12V	7.2V 14.4V 9.6V 18V 12V 24V	7.2V	7.2V 10.8V	7.2V 14.4V 9.6V 18V 12V	36V only
		Low Voltage Part no	193877-1	-	193848-8	-	-	-	630506-0	194869-3
		220 - 240 (2pin type) Part no	193864-0	192935-0	193827-6	194164-1	194320-3	630584	-	-
		220-240 (3pin type) Part no	193865-8	192808-7	193828-4	194165-9	-	-	630507-8	194864-3
										
NI-Cd (Stick)	Battery	Part no	V/Ah							
	7000	 191679-9	7.2V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*30 Minutes
	9000	 191681-2	9.6V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*30 Minutes
	9100	 192019-4	9.6V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*30 Minutes
	9120	 192638-6	9.6V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*30 Minutes
	9122	 192595-8	9.6V 2.0 Ah	45 Minutes	14 Minutes	45 Minutes	*20 Minutes	-	-	*45 Minutes
	1200	 192271-4	12V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*45 Minutes
	1202	 192536-4	12V 2.0 Ah	45 Minutes	14 Minutes	45 Minutes	*20 Minutes	-	-	*45 Minutes
	1220	 192681-5	12V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*30 Minutes
	1222	 192597-4	12V 2.0 Ah	45 Minutes	14 Minutes	45 Minutes	*20 Minutes	-	-	*45 Minutes
NI-Cd (Cluster)	1420	 193062-6	14.4V 1.3 Ah	30 Minutes	9 Minutes	30 Minutes	*13 Minutes	-	-	*30 Minutes
	1422	 192600-1	14.4V 2.0 Ah	45 Minutes	14 Minutes	45 Minutes	*20 Minutes	-	-	*45 Minutes
	PA18	 194105-7	18V 1.3 Ah	-	-	30 Minutes	*13 Minutes	-	-	*30 Minutes
	1822	 192827-3	18V 2.0 Ah	-	-	45 Minutes	*20 Minutes	-	-	*45 Minutes
	B7010	 194355-4	7.2V 1.3 Ah	-	-	-	-	30 Minutes	30 Minutes	-
	BL1013	 194550-6	10.8V 1.3 Ah	-	-	-	-	-	50 Minutes	-
Lithium-ion	BL1830	 638409-2	18V 3.0 Ah	-	-	-	30 Minutes	-	-	22 Minutes
	BL3626	 194873-2	36V 2.6 Ah	-	-	-	-	-	-	22 Minutes

* Use with interchangeable adapter ADP04 193947-6 (optional accessory).
Automatic Refreshing Adapter ADP03 193682-6 (optional accessory).