

OZ-SS-105LM1,200

✕ OBSOLETE


OEG

TE Internal #: 1461251-3

TE Internal Description: OZ-SS-105LM1,200

STD SCHRACK RZF Power Relays

[View on TE.com >](#)



All STD SCHRACK RZF Power Relays (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought



TE Part #3-1393237-3
RTE24024F



TE Part #1558666-3
T9GS1L14-12



TE Part #4-1419144-7
OJE-SH-112HMF,F095



TE Part #749809-9
KIT,PLUG,25P,HDE



TE Part #3-1393127-8
PRD-11DG0-24=PRD




TE Part #5747461-3
HD-20 RCPT 25P RA 590 THD INS



TE Part #2-1440002-8
OZ-SS-124L,200



TE Part #1649399-4
OZ-SS-112L1,200



TE Part #2-2158100-2
RZL3-1C4-L012-R



TE Part #5-1440002-8
PCF-124D2M,000

Documents

Product Drawings

OZ-SS-105LM1,200

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1461251-3_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1461251-3_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1461251-3_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

OZ_OZT Series Relay Data Sheet - English

English

Product Specifications

Product Specification

Japanese

Definitions General Purpose Relays

English