

00 21 30

Tool Case for electrical contractors 23 parts



- contains 23 brand name quality tools, partly VDE tested according to DIN EN/IEC 60900
- hard-wearing ABS hard-shell construction with aluminium frame and circular buffer protection
- document compartment and pen holding straps
- one removable tool plate, with elastic loops on both sides
- one cover plate with elastic loops and tool protection cloth
- large base tray with variable separations (e.g. for measuring and testing devices). Interior dimensions: 420 x 320 x 85 mm
- sturdy metal locks and 3-digit-lock
- strong, ergonomic handle
- feet on both sides
- colour: silver / aluminium look

















Article No.	00 21 30
EAN	4003773051084
Net weight g	9440

technical change and errors excepted



Content 00 21 30 (23)

Article No.			Quantity	Nominal size	
00 11 03	Knipex	Control Cabinet Key, for all standard cabinets and shut-off systems	1	76 mm	
03 06 180	Knipex	Combination Pliers	1	180 mm	
12 40 200	Knipex	Self-Adjusting Insulation Stripper	1	200 mm	
16 80 125 SB	Knipex	Universal Dismantling Tool	1	125 mm	
26 16 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
26 26 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	

70 06 125	Knipex	Diagonal Cutter	1	125 mm	
70 06 160	Knipex	Diagonal Cutter	1	160 mm	
86 03 180	Knipex	Pliers Wrench, pliers and a wrench in a single tool	1	180 mm	
87 03 250	Knipex	KNIPEX Cobra®, Hightech Water Pump Pliers	1	250 mm	
92 27 62	Knipex	Precision Tweezers, insulated	1	150 mm	
98 56	Knipex	Cable Knife, with replaceable blade	1	185 mm	
006100	Wera	Screwdrivers for slotted screws, 160i	1	0,4 x 2,5 x 80 mm	
006110	Wera	Screwdrivers for slotted screws, 160i	1	0,6 x 3,5 x 100 mm	
006115	Wera	Screwdrivers for slotted screws, 160i	1	0,8 x 4,0 x 100 mm	
006120	Wera	Screwdrivers for slotted screws, 160i	1	1,0 x 5,5 x 125 mm	
006125	Wera	Screwdrivers for slotted screws, 160i	1	1,2 x 6,5 x 150 mm	
006130	Wera	Screwdrivers for slotted screws, 160i	1	1,2 x 8,0 x 175 mm	
006150	Wera	Screwdrivers for cross recessed Phillips® screws, 162i PH	1	PH0 x 80 mm	
006152	Wera	Screwdrivers for cross recessed Phillips® screws, 162i PH	1	PH1 x 80 mm	
006154	Wera	Screwdrivers for cross recessed Phillips® screws, 162i PH	1	PH2 x 100 mm	
006162	Wera	Screwdrivers for cross recessed Pozidriv® screws, 165i	1	PZ1 x 80 mm	
006164	Wera	Screwdrivers for cross recessed Pozidriv® screws, 165i	1	PZ2 x 100 mm	