

Technical data sheet

Article number:
151-01458

RCB90SM10



Product Group	Ratchet P-Clamp
Product Family	For bundle diameters from 12.7 mm to 19.5 mm, B-Series
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV), Steel (ST), Zinc plated (ZN)
Colour	Black (BK)
Bundle Ø max.	19.5 mm
Bundle Ø min.	12.7 mm
CE Certification	No
Fixation Method	Screw Mounting
Flammability	UL 94 HB
for Hole Ø (FH)	10.29 mm
Length (L)	101.9 mm
Length (L2)	68.8 mm
Min.Tensile Strength	445 N
Operating Temperature	-40 °C to +105 °C
Package Content	280 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UL-File Number	E64139
UV-Stabilised	Yes
Variant	Short
Width (W)	34.9 mm

