

Features

- Easy to apply
- Push fit on thread
- ½-turn to lock
- Unscrew to release
- Will not corrode
- Will not conduct electricity

RS PRO Hex Nuts

RS Stock No.: See Table



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- These KWIK Nuts are designed to offer a quick, easy and secure fastening method
- Parts are pushed onto threaded studs, screws or rods and ½-turned to lock
- Simply unscrew to release
- Can be installed by hand
- Ideal for lightweight fastening applications
- Will not corrode or conduct electricity

Material Specifications

| | |
|---------------------------|----------------|
| Materials | Nylon 66 |
| Nut Type | Hex Nut |
| Type | KWIK Nut |
| Colour | Black |
| Finish | Plain |
| Flammability Rating | UL94-V2 |
| Working Temperature Range | -40°C to +85°C |
| Imperial or Metric | Metric |

Part Specifications

| Parameters | 0304036 | 0304038 | 0304039 | 0304041 | 0304042 |
|---------------------|---------|---------|---------|---------|---------|
| G (Thread Size) | M3 | M4 | M5 | M6 | M8 |
| ØD (Knurl Diameter) | 8.1mm | 9.7mm | 12.1mm | 15.0mm | 20.0mm |
| SW (Across Flats) | 6.9mm | 7.9mm | 9.9mm | 12.7mm | 17.0mm |
| H (Overall Height) | 4.2mm | 4.8mm | 5.8mm | 6.9mm | 8.6mm |
| A (Knurl Height) | 1.9mm | 2.0mm | 2.1mm | 2.6mm | 3.0mm |

