



DX4 DETACHABLE HOLSTER POCKET TROUSERS

DESCRIPTION

The DX4 Holster Trousers are ergonomically designed and use the targeted placement of dynamic 4X stretch fabrics to give maximum range of movement when working. The trousers feature a high-rise back waistband with side elastication, ensuring protection in all working positions. Pre-bent top loading adjustable knee pad pockets, generously sized front pockets and multi-functional zip thigh pockets offer secure storage of phone, pens and tools. Triple stitching throughout for maximum durability.

COMPOSITION

-  **Titanmill Pro Stretch: 93% Polyester, 7% Elastane, 270g**
-  **65% Polyester, 35% Cotton Ripstop Weft Stretch, 230g**
-  **CorePro: 87% Nylon, 13% Elastane, 245g**
-  **Metro Blue 28-48**

FEATURES

- 4-way stretch fabric for ease of movement and added comfort
- High rise back waistband ensures protection in all working positions
- Reflective trim for increased visibility and safety
- Zip off holster pockets for added versatility
- Two tier knee pad pockets allowing two positioning options
- Multiple side zip compartments for secure storage
- 16 pockets for ample storage
- 2 side zip pockets for secure storage
- Smart phone pocket
- Hammer loop for secure storage of work tools
- 2 Back pockets
- 2 Zipped thigh pockets

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
DX440MBR	METRO BLUE	28-14

FEATURES



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



16 POCKETS
16 pockets for ample storage



TECHINCAL INFORMATION



- Do not iron the reflective tape
- Wash dark colours separately
- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash reflective tape on the inside
- Wash with similar colours

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
DX440MBR28	Metro Blue	65	45	36	1.110	5850.000	5036108326235	15036108815019
DX440MBR30	Metro Blue	65	45	36	1.165	5850.000	5036108326242	15036108815026
DX440MBR32	Metro Blue	65	45	36	1.130	5850.000	5036108326259	15036108815033
DX440MBR33	Metro Blue	65	45	36	1.202	5850.000	5036108326266	15036108815040
DX440MBR34	Metro Blue	65	45	36	1.130	5850.000	5036108326273	15036108815057
DX440MBR36	Metro Blue	65	45	36	1.160	5850.000	5036108326280	15036108815064
DX440MBR38	Metro Blue	65	45	36	1.170	5850.000	5036108326297	15036108815071
DX440MBR40	Metro Blue	65	45	36	1.200	5850.000	5036108326303	15036108815088
DX440MBR41	Metro Blue	65	45	36	1.262	5850.000	5036108326310	15036108815095
DX440MBR42	Metro Blue	65	45	36	1.286	5850.000	5036108326327	15036108815101
DX440MBR44	Metro Blue	65	45	36	1.250	5850.000	5036108326334	15036108815118
DX440MBR46	Metro Blue	65	45	36	1.270	5850.000	5036108326341	15036108815125
DX440MBR48	Metro Blue	65	45	36	1.320	5850.000	5036108326358	15036108815132