



**Part Number :** [797582146](#)

**Product Description :** Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black

**Series Number :** 79758

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies

---

## Documents & Resources


### Drawings

[797582146\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant   |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21   |
| REACH SVHC         | Not Contained per D(2024)7663-DC (21 Jan 2025)   |
| EU RoHS            | Compliant per EU 2015/863  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|                        |   |
|------------------------|---|
| Status                 | Active  |
| Category               | Power and Signal Cable Assemblies   |
| Series                 | 79758   |
| Description            | Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black |
| Assembly Configuration | Pre-crimped Lead Only   |
| Connector to Connector | KK Plus 396 Crimp Terminals   |
| Keyword                | Pre-Crimped Leads   |
| Product Name           | KK Plus   |
| UPC                    | 193264168682  |

#### Physical

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 300.00mm             |
| Circuits (Loaded)              | 1                    |
| Circuits (maximum)             | 1                    |
| Color - Resin                  | Black                |
| Gender                         | Female-Female        |
| Material - Metal               | Copper Alloy         |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 5.264/g              |
| Packaging Type                 | Bag                  |
| Single Ended                   | No                   |
| Termination Interface Style    | Crimp or Compression |
| Wire/Cable Type                | UL 1015              |
| Wire Size (AWG)                | 18                   |

## Mates With / Use With

### Use with Part(s)

| Description                                | Part Number   |
|--|---------------|
| KK 3.96mm Crimp Housings                   | <u>41695</u>  |
| KK 3.96mm Pitch Single Row Crimp Housings  | <u>6442</u>   |
| KK Plus 396 Single Row Receptacle Housings | <u>207458</u> |

---

This document was generated on Nov 05, 2025