

INSULATED SPANNER & SCREWDRIVER SET FOAM3 17 PIECES



- Approved for live working up to 1,000 volts
- Spanners with open off set at 15° for easier use
- Screwdrivers with Integrated protective insulation with two colours clearly indicates if there is any damage
- Insulated Knife with blade protector and replaceable blade
- Tools are hold in place using three colour pre-cut high-density EVA foam
- Design to fit exactly in TengTools service cases
- Design and manufactured to DIN3114, 2380 and IEC60900
- Organised in a foam inlay module size 3 (FOAM3)

Insulated Spanner & Screwdriver Set FOAM3 17 Pieces

General information

Country of origin: Taiwan
Barcode: 5020385011670
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC011815
UNSPSC: 27111706

Dimensions

Net weight (g): 1248
Width (mm): 433
Depth (mm): 267
Height (mm): 47

Attributes

Product type: Spanners & Wrench Sets, Screwdriver Sets, Insulated Tool Sets
Certificates: VDE
Number of pieces: 17
Handle type: Bi-material
Insulated: Yes
Unit of measurement: Metric
Inlay material: FOAM
Type of set: FOAM3

Features



Technical changes and errors may occur. 01-08-2024 19:59



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås, Sweden

LIST OF CONTENTS



TEFXV17 Insulated Spanner & Screwdriver Set FOAM3 17 Pieces

- MDV824N** Flat Insulated Screwdriver 0.8 × 4.0 mm
- MDV826N** Flat Insulated Screwdriver 1.0 × 5.5 mm
- MDV842N** PH Insulated Screwdriver PH1
- MDV844N** PH Insulated Screwdriver PH2
- MDV864N** PZ Insulated Screwdriver PZ2
- MKV709** Insulated Knife
- MKV709A** Replacement Blades For Insulated Knife
- MPV600508** Insulated Spanner 8 mm
- MPV600510** Insulated Spanner 10 mm
- MPV600512** Insulated Spanner 12 mm
- MPV600513** Insulated Spanner 13 mm
- MPV600514** Insulated Spanner 14 mm
- MPV600517** Insulated Spanner 17 mm
- MPV600519** Insulated Spanner 19 mm