

Technical data sheet

Article number:
112-00083

SPH275

Product Group	Cable ties with low profile head
Product Family	SPH-Series
Material	Polyamide 6.6 recycled, high impact modified, UV-stabilised (PA66HIRUV(REC))
Colour	Black (BK)
Bundle Ø max.	62 mm
Bundle Ø min.	25 mm
Flammability	UL 94 HB
Halogen-free	Yes
Length (L)	262 mm
Min.Tensile Strength	800 N
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Package Content packed in	bag
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.26 mm
Variant	Outside Serrated
Weight/Unit	0.0046 kg
Width (W)	9 mm

HF ✓

RoHS ✓