

Circular Saw XGT®

RS002G

40V max • 4 000 min⁻¹ • 260 mm

Highly robust circular saw for demanding applications

40V max XGT® Li-ion battery and brushless motor makes this saw excellent choice for demanding applications. The blade can reach up to 4 000 min⁻¹ to ensure high cutting performance with large cutting capacity. Vacuum remote startup function (AWS) and XPT for improved dust and water resistance.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	4000 min ⁻¹
Max. Cutting Depth at 90°	95 mm
Max. Cutting Depth at 45°	70 mm
Max. Cutting Depth at 56°	54,5 mm
Max. Bevel Range (Left)	0 - 56 °
Sound Power Level (L _{WA})	107 dB(A)
Sound Pressure Level (L _{pA})	99 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	489 x 193 x 309 mm
Tool weight with battery	5,7 - 6,9 kg
Blade Diameter	260 mm
Bore Size (Arbor Diameter)	25 / 30 mm

User benefits

- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Retractable, extra-wide tool hook secures the tool when not in use
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Soft start for smooth start-ups

Link to product - www.makitauk.com



Related products

■ Optional AC

165153-3

Parallel Guide



■ Other

User manual

Parts drawing