



## Datasheet

# 2 in 1 USB Magnifying LED Lamp

Stock number: 189-9349

EN



### Specifications:

Material of primary lens: Glass

Dioptre of primary lens (D): 3

Primary lens size (mm) **length/Φdiameter**: 100 Light source voltage (V): 5

Light source power (W): 2.5

Lumen (lm): 250

Light source quantity (pcs): 36

Material of cove: ABS

Color of cove: White

Clamp Max. opening (mm) : 55

Base size (mm) L×W×H: 132x132

Power cord: Micro USB Cable

Power cord length (cm): 100

Standard accessories: Manual : Chinese and English

[rspro.com](http://rspro.com)

Features:

**2 in 1 Design -**

Interchangeable base and clamp for greater versatility.  
With 3D magnification lens, it can be a magnifier as well.

**User Friendly -**

Touch switch provides easy control.  
Flexible goose neck helps to position the light and magnifier perfectly.  
USB powered design breaks the space limit  
Warm and cold light switchable with stepless brightness control offer user convenience.

**Energy Efficient**

Low power consumption, replace 25W halogen bulb by 2.5W LED.  
Instant full light, no need to wait for warming up the lamp.

[rspro.com](http://rspro.com)