

LONG LIFE DRILLING IN METAL

PRO

- 1 High-speed steel ground for long-lasting performance
- 2 Split-point tip for starting holes exactly where you need them



* vs Bosch 2608577167



BOSCH

PRO METAL HSS-G TWIST DRILL BIT SET

PRO


- For drilling in metal, eg when pre-drilling for anchors, rivets, and threads or drilling in steel beams for installations, and fixtures
- Highly efficient for construction workers and installers: Long Life
- Lasts up to 2x longer than a Bosch PointTeQ Drill Bit
- Cylindrical shank compatible with three-jaw drill chucks



PRODUCT PROPERTIES						ORDERING INFORMATION					
Diameter mm	Working length mm	Total length mm	Set size	Set dimension(s) mm	X-LOCK	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number	
5-piece PRO Metal HSS-G Twist Drill Bit Set5-piece PRO Metal HSS-G Twist Drill Bit Set											
2.0	24	49			-	P2a	1	1	323 628	2 607 019 114	
3.0	33	61									
4.0	43	75									
5.0	52	86									
5.0	52	86									
6-piece PRO Metal HSS-G Twist Drill Bit Set6-piece PRO Metal HSS-G Twist Drill Bit Set											
2.0	24	49	A	156.5 x 69.5 x 23	-	P1k	6	1	446 136	2 607 010 529	
3.0	33	61									
4.0	43	75									
5.0	52	86									
6.0	57	93									
6.0	57	93									
7-piece PRO Metal HSS-G Twist Drill Bit Set7-piece PRO Metal HSS-G Twist Drill Bit Set											
2.0	24	49		141.0 x 80.0 x 20	-	P1k	7	1	784 863	2 608 589 295	
3.0	33	61									
4.0	43	75									
5.0	52	86									
6.0	57	93									
8.0	75	117									
8.0	75	117									
10-piece PRO Metal HSS-G Twist Drill Bit Set10-piece PRO Metal HSS-G Twist Drill Bit Set											
1.0	12	34	B	156.5 x 106.5 x 23	-	P1k	10	1	446 198	2 607 010 535	
2.0	24	49									
3.0	33	61									
4.0	43	75									
5.0	52	86									
6.0	57	93									
7.0	69	109									
8.0	75	117									
9.0	81	125									
9.0	81	125									
13-piece PRO Metal HSS-G Twist Drill Bit Set13-piece PRO Metal HSS-G Twist Drill Bit Set											
1.5	18	40	C	124.0 x 106.5 x 23	-	P1k	13	1	446 228	2 607 010 538	
2.0	24	49									
2.5	30	57									
3.0	33	61									
3.2	36	65									
3.5	39	70									
4.0	43	75									
4.5	47	80									


BOSCH

PRO METAL HSS-G TWIST DRILL BIT SET

PRO

PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter mm	Working length mm	Total length mm	Set size	Set dimension(s) mm	X-LOCK	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number
4.8	52	86								
5.0	52	86								
5.5	57	93								
6.0	57	93								
6.0	57	93								
18-piece PRO Metal HSS-G Twist Drill Bit Set						18-piece PRO Metal HSS-G Twist Drill Bit Set				
1.0	12	34		180.0 x 85.0 x 45	-	P1k	18	1	430 210	2 607 019 578
1.5	18	40								
2.0	24	49								
2.0	24	49								
2.5	30	57								
3.0	33	61								
3.0	33	61								
3.5	39	70								
4.0	43	75								
4.0	43	75								
4.5	47	80								
5.0	52	86								
5.5	57	93								
6.0	57	93								
7.0	69	109								
8.0	75	117								
9.0	81	125								
9.0	81	125								
19-piece PRO Metal HSS-G Twist Drill Bit Set						19-piece PRO Metal HSS-G Twist Drill Bit Set				
1.0	12	34		172.0 x 115.0 x 42	-	P1k	19	1	689 779	2 608 587 013
1.5	18	40								
2.0	24	49								
2.5	30	57								
3.0	33	61								
3.5	39	70								
4.0	43	75								
4.5	47	80								
5.0	52	86								
5.5	57	93								
6.0	57	93								
6.5	63	101								
7.0	69	109								
7.5	69	109								
8.0	75	117								
8.5	75	117								
9.0	81	125								
9.5	81	125								
9.5	81	125								
25-piece PRO Metal HSS-G Twist Drill Bit Set						25-piece PRO Metal HSS-G Twist Drill Bit Set				
1.0	12	34		200.0 x 115.0 x 58	-	P1k	25	1	689 816	2 608 587 017
1.5	18	40								
2.0	24	49								
2.5	30	57								
3.0	33	61								
3.5	39	70								
4.0	43	75								
4.5	47	80								
5.0	52	86								
5.5	57	93								
6.0	57	93								
6.5	63	101								
7.0	69	109								


BOSCH

PRO METAL HSS-G TWIST DRILL BIT SET

PRO

PRODUCT PROPERTIES					ORDERING INFORMATION			
Diameter mm	Working length mm	Total length mm	Set size	Set dimension(s) mm	Packaging type	Pack quantity	Minimum order quantity	Barcode
7.5	69	109		X-LOCK				3 165 140...
8.0	75	117						
8.5	75	117						
9.0	81	125						
9.5	81	125						
10.0	87	133						
10.5	87	133						
11.0	94	142						
11.5	94	142						
12.0	101	151						
12.5	101	151						
12.5	101	151						


BOSCH