



Cordless MULTIMASTER AMM 700 Max Top

Battery-powered oscillating multi-tool

Our best MultiTool for the most rapid work progress in interior work and renovation with 60 accessories – from sawing in wood, metal and plastics, to cutting out tiles, cutting silicone joints and carpets, removing adhesive residues and tile adhesive.

Product number: 7 129 34 61 00 0

Details

- › Anti-vibration system: continuously safe and pleasant working thanks to minimal vibrations and outstanding noise insulation.
- › StarlockMax tool mounting: more work progress and greater precision thanks to 100% power transmission without losses.
- › QuickIN: tool changes in less than 3 seconds thanks to the patented tool-free FEIN rapid clamping system.
- › With the StarlockMax tool mounting, you can access around 180 FEIN accessories from the Starlock, Starlock Plus and StarlockMax performance classes.
- › 18 V FEIN PowerDrive motor: very powerful and virtually wear-free, brushless motor offering great efficiency, ability to handle extreme loads and a long service life.
- › Metal gearbox: ability to withstand high loading and outstanding service life because all the gearbox parts are made from metal.
- › Mechanical interface: for stationary operation in the table or drill jig holder or for securing the depth stop.
- › SafetyCell technology: perfect protection against overload, overheating and total discharge thanks to Li-ion batteries with individual cell monitoring.
- › The battery charge can be read off the battery.

Price includes

- ✓ 2 E-Cut standard saw blades curved (35 mm)
- ✓ 1 E-Cut precision saw blade (35 mm)
- ✓ 1 E-Cut long-life saw blade (10 mm)
- ✓ 1 E-Cut long-life saw blade (32 mm)
- ✓ 1 E-Cut carbide Pro saw blade (32 mm)
- ✓ 1 HSS segment saw blade
- ✓ 1 Stopper knife
- ✓ 1 Multi-function knife
- ✓ Sanding sheets, perforated (10 each of grit 60, 80, 120, 180)
- ✓ 1 rapid charger ALG 80
- ✓ 1 plastic carrying case
- ✓ 2 E-Cut standard saw blades curved (65 mm)
- ✓ 1 E-Cut precision saw blade (65 mm)
- ✓ 2 E-Cut long-life saw blades (35 mm)
- ✓ 1 E-Cut long-life saw blade (42 mm)
- ✓ 1 segmented saw blade (Ø 85 mm)
- ✓ 1 HM rasp (triangular)
- ✓ 1 Cutter blade, mushroom shaped
- ✓ 1 Sanding plate with holes
- ✓ 1 dust extraction device
- ✓ 2 Li-ion battery packs (18 V / 3 Ah)

Product feature

- ✓ Mechanical interface



Technical data

TECHNICAL DATA

Battery voltage	18 V
Battery capacity	3 Ah
Battery compatibility	Li-ion / HighPower Li-ion
Battery interface	MultiVolt
Oscillations	10,000 - 19,500 rpm
Tool Holder	StarlockMax
Tool change	QuickIN
Amplitude	2 x 2,0°
Weight with battery	1.60 kg
Weight without storage battery	1.10 kg

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA Uncertainty of measured value KpA	83 dB 3 dB
Sound power level LWA Uncertainty of measured value KWA	94 dB 3 dB
Sound peak value LpCpeak Uncertainty of measured value KpCpeak	97 dB 3 dB

Application examples

