




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Female Screwlock Assembly Kit**

Hardware Accessory Function: **Latching, Locking & Retention**

Features

Product Type Features

Connector Hardware Accessory Type	Female Screwlock Assembly Kit
Hardware Accessory Function	Latching, Locking & Retention

Mechanical Attachment

Thread Size	4-40 UNC
-------------	----------

Dimensions

Thread Length	7.92 mm[.312 in]
Product Feature Length	12.7 mm[.5 in]

Packaging Features

Packaging Method	Individual
Packaging Quantity	2

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025 (247)

SVHC > Threshold:

Pb (.26% in M-2544-1)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | AMPLIMITE Kit

Customers Also Bought







TE Part #5175472-1
CHAMP 050 BTB PLUG H W/LEG 20P



TE Part #3-917360-0
1.25 AF REC ASSY 30P B/TRAY




TE Part #172038-1
MIC CAP 11P H



TE Part #171838-1
MIC PLUG 21P W/CIRCUIT NUMBER

TE Part #1108780-1
MDL2-GR.O-8.B1-4



TE Part #2-1437144-7
FSN-23A-11=NOMEX FS STD

Documents

Product Drawings

AMPLIMITE SCREWLOCK KIT

English

CAD Files

Customer View Model

ENG_CVM_CVM_172616-1_J1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172616-1_J1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_172616-1_J1.2d_dxf.zip

English

3D PDF

3D

3D PDF

English

Customer View Model

ENG_CVM_172616-1_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_172616-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_172616-1_J.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping Drawer Connector Contacts

English

Application Specification

English