



Plummer block housing units

PSHE25-XL-N (Series PSHE)

cast iron housing, radial insert ball bearing with eccentric locking collar, P seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (<http://www.ina.de/content.ina.de/en/mediathek/library/library.jsp>) or by telephone on +49 (91 32) 82 - 28 97.

d	25 mm
L	70 mm
H ₂	70 mm
A	36 mm
A ₁	21 mm
B ₁	31 mm
d ₃ max	37,5 mm
H	36,5 mm
J	50,8 mm
K	M10
Q	M6
S ₁	23,5 mm
m	0,54 kg Mass
C _r	14900 N Basic dynamic load rating, radial
C _{0r}	7800 N Basic static load rating, radial
	SHE05 Designation of housing
	GRAE25-XL-NPP-B Designation of bearing
	KASK05 Bearing end cap, closed design. To be ordered separately.
	Slot for bearing end cap

