




Y	10	52.24	34.29	48.29	41.29		18.4	4		9	2-	-8
X	10	52.24	34.29	48.29	41.29		18.4	4		9	1-	-8
	8	44.62	26.67	40.67	33.67		18.4	4		7	1-	-7
	5	33.19	15.24	29.24	22.24		18.4	4		4	1-	-5
Y	3	25.57	7.62	21.62	14.62		8.4	2		2	2-	-3
X	3	25.57	7.62	21.62	14.62		8.4	2		2	1-177648-3	
キータイプ	POS. 極数	寸法	A	B	C	D	F	G		N	型番	PART NUMBER

Copyright © 1992 年 AMP (Japan) LTD. ALL RIGHTS RESERVED.				Copyright © 1992 AMP (Japan) LTD. ALL RIGHTS RESERVED.				AMP 日本エー・エム・ピー株式会社 Tokyo, Japan			
B REVISED (FJ00-3700-95) KI Y.I 24/NOV 95				A1 REVISED (FJ00-2011-95) NM S.M 3/30 95				A REVISED (FJ00-0685-94) KI S.M 9/27 94			
O RELEASED J-1533 NM S.M 11/16 92				LTR 変更 (REVISION RECORD) DR CHK DATE				DR. 9 NOV 92 DE. 9 NOV 92			
CHK. 16 NOV 92 APP. 16 NOV 92				S. MANABE S. MANABE				名称 (NAME) フリーハンギングタイプタブハウジング ダイナミック D3100S シリーズ用 WIRE TO WIRE TAB HSG FOR DYNAMIC 3100 (SINGLE ROW)			
一般公差 (GENERAL TOLERANCE)				10mm以下: ±0.2 10mm以上 30mm以下: ±0.25 30mm以上 100mm以下: ±0.3 ★ 注: ±3°				SIZE LOC 番号 (No.)			
B J				177648				尺度 (SCALE) 2/1			
REV. B				SHEET 1 OF 1							