

ball valve

VZBD-1-S1-16-T-2-F0405-V14V14

Part number: 4795668

FESTO

Stainless steel for use in the cosmetics and pharmaceutical industry, 2/2-way, nominal width 1", top flange F0405, PN16, clamp ferrule to ASME-BPE, electropolished.

Festo is only a retailer of this product, not the manufacturer.



Data sheet

Feature	Value
Design structure	2-way ball valve
Type of actuation	mechanical
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	Clamp in accordance with ASME-BPE
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F0405
Inside diameter	22.1 mm
Nominal diameter DN	25
Valve function	2/2
Flow direction	reversible
Nominal pressure of process valve	16
Breakaway torque at differential pressure, nominal pressure, process valve PN	15 Nm
Based on the standard	ASME BPE ISO 5211
Medium	Vapour Compressed air in accordance with ISO8573-1:2010 [-:~:] Inert gases Water Neutral fluids
Medium temperature	-20 ... 200 °C
Flow rate Kv	19.8 m3/h
Materials note	Contains PWIS substances Conforms to RoHS
Food-safe	See Supplementary material information
Material housing	Stainless steel casting
Material number for housing	1.4409
Material seat seal	PTFE, modified
Material seals	FPM PTFE
Material ball	Stainless steel casting
Material number for ball	1.4409
Material shaft	High alloy steel, non-corrosive
Material number for shaft	1.4401
Product weight	950 g
Authorisation	3-A Sanitary CRN
Corrosion resistance classification CRC	4 - Very high corrosion stress