

Rittal – The System.

Faster – better – everywhere.

Acrylic glazed cover – FT 2780.000

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Acrylic glazed cover – FT 2780.000

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Design:	482.6 mm (19")
Description:	With security lock, lock no. 3524 E
Material:	Frame: Extruded aluminium sections with die-cast corner pieces Glass panel: Smoked acrylic
Protection category IP to IEC 60 529:	IP 54
Supply includes:	Hinges and assembly parts. Lock insert no. 3524 E

Product description

Dimensions:	Width: 320 mm Height: 158 mm Depth: 47.5 mm
Viewing area:	Width: 280 mm Height: 137.5 mm
Installation dimensions:	Installation width: 269,2 mm / 1/2 19" Installation height: 3 U
Build depth for components (max.):	43 mm
Packs of:	1 pc(s).
Weight/pack:	1.08 kg

Copper weight (kg per piece):	0
EAN:	4028177032217
Customs tariff number:	76101000
ETIM 7.0:	EC002527
ETIM 6.0:	EC002527
eCl@ss 8.0/8.1:	27182301
eCl@ss 6.0/6.1:	27182301
Product description:	FT Acrylic glazed cover, 482.6 mm (19"), WHD: 320x158x47,5 mm
Approvals	
Certificates:	NA