



DCG426N

18V XR Brushless Die Grinder Naked

Selling Proposition

- 18V Brushless motor improved performance in demanding applications
- 3-Step speed dial Improved application control
- Dual position variable speed switch Improved gripping area and speed control
- LED nose ring Improved work piece visibility
- Mesh guard reduces motor contamination
- Durable textured rubber nose Increased comfort and control

Standard Equipment

- 6mm Collet
- Spanner

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	1000 Watts
Power Output	760 Watt
No Load Speed	0 - 5,000/ 17,500/ 25,000 rpm
Max. Disc Diameter	38 mm
Spindle Thread	M15
Weight	1.19 kg
Length	380 mm
Height	85 mm