

Features

- *Conductor*
Material: 100% copper wires
- *Jacket Material:*
PVC, black
- *Cable Length:* 2M
- *Easy to install and reliable connection*
- *Color:* Black

RS PRO Telephone Cable

RS Stock No.: 0707869



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

It is a RJ45 8P8C male to RJ45 8P8C male cable. Easy to be installed and no static or distortion of voice. Connect a computer to router or server or network equipment. 100% copper 8 conductors black wire.

General Specifications

<i>Number of Strands</i>	<i>8</i>
<i>Conductor Strand Type</i>	<i>Stranded</i>
<i>Terminated/Unterminated</i>	<i>Terminated; Unterminated</i>
<i>Connector Type</i>	<i>Male RJ45/RJ45</i>
<i>Connector B</i>	<i>Male RJ45</i>
<i>Connector A</i>	<i>Male RJ45</i>
<i>Outer Sheath Material</i>	<i>PVC;</i>
<i>Sheath Colour</i>	<i>Black</i>
<i>Conductor Material</i>	<i>Bare Copper</i>
<i>Drain Wire</i>	<i>No</i>
<i>Fire Behaviour</i>	<i>Flame Retardant.</i>

Mechanical Specifications

<i>Length</i>	<i>2m</i>
<i>Outer Diameter</i>	<i>7.1*2.2mm</i>
<i>Sheath Thickness</i>	<i>0.6mm</i>
<i>Insulator Diameter</i>	<i>0.9mm +/-0.05</i>
<i>American Wire Gauge</i>	<i>28AWG</i>

<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

