

IPD P 5P2,5 M BK - Connector



1088667

<https://www.phoenixcontact.com/in/products/1088667>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, product family: IPD, connection method: Push-lock connection, number of positions: 4+PE, Pin, 0.5 mm² ... 2.5 mm², 600 V, 17.5 A, PA, black, coding: P, external cable diameter: 7 mm ... 11 mm and 11 mm ... 16 mm

Your advantages

- Easy distribution of power, as components are plugged directly
- Simple, time-saving wiring in the field with Push-Lock connection
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system
- Secure, tool-free locking even in particularly difficult installation situations
- Fast commissioning with preassembled cable assemblies

Commercial data

Item number	1088667
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF6JCA
GTIN	4055626890845
Weight per piece (including packing)	73 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



Technical data

Notes

General

NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

Product properties

Product type	Installation connector
Product family	IPD
Number of positions	5
Connection profile	4+PE
Position marking	1, 2, 3, N, PE
Number of connections per position	1
Coding	P

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	17.5 A
Rated voltage (III/3)	600 V
Nominal voltage U_N	600 V AC 600 V DC
Nominal current I_N	17.5 A

Connection data

Connection technology


Connection method On the field side	Push-lock connection
-------------------------------------	----------------------

Conductor connection

Conductor cross section flexibel	0.5 mm ² ... 2.5 mm ²
Conductor cross section solid	0.5 mm ² ... 2.5 mm ²
Conductor cross section with ferrule	0.5 mm ² ... 2.5 mm ²
Connection cross section AWG	20 ... 14

Dimensions

Dimensional drawing



IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



Width	32.5 mm
Height	32.1 mm
Length	91.7 mm

Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PA
Material Seal	NBR
Flammability rating according to UL 94	V0
Contact material	Cu
Contact surface material	Ni/Ag/Sn

Cable/line

External cable diameter	7 mm ... 11 mm
	11 mm ... 16 mm
Position marking	1, 2, 3, N, PE

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50 (IP66/IP68/IP69K)
	100 (IP66)


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
	Touch-proof when not plugged in (IP2X)
Impact strength	IK07
Ambient temperature (operation)	-30 °C ... 100 °C
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-30 °C ... 100 °C
Resistance to UV radiation	yes


Drawings

Diagram



Derating diagram for 2.5 mm²


Dimensional drawing




IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



Derating diagram for 1.5 mm²



Derating diagram for 1.0 mm²

IPD P 5P2,5 M BK - Connector


1088667


<https://www.phoenixcontact.com/in/products/1088667>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1088667>

**VDE Zeichengenehmigung**
Approval ID: 40059408

 cULus Listed Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Only rigid conductors	600 V	20 A	- 14	-
multi-stranded with ferrule	600 V	20 A	- 14	-

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



Classifications

ECLASS

ECLASS-11.0	27440605
ECLASS-12.0	27440605
ECLASS-13.0	27440605

ETIM

ETIM 9.0	EC002560
----------	----------

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



Mandatory accessories

IPD PL 5P2,5 F BK - Connector

1088670

<https://www.phoenixcontact.com/in/products/1088670>



Connector, product family: IPD, connection method: Push-lock connection, number of positions: 4+PE, Socket, 0.5 mm² ... 2.5 mm², 600 V, 17.5 A, PA, black, coding: P, external cable diameter: 7 mm ... 11 mm and 11 mm ... 16 mm

IPD PL 5P2,5 F A0,5 PVC GY - Connecting cable

1526880

<https://www.phoenixcontact.com/in/products/1526880>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 0.5 m, Socket straight, on free cable end

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



IPD PL 5P2,5 F A1,0 PVC GY - Connecting cable

1526882

<https://www.phoenixcontact.com/in/products/1526882>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 1 m, Socket straight, on free cable end

IPD PL 5P2,5 F A3,0 PVC GY - Connecting cable

1526885

<https://www.phoenixcontact.com/in/products/1526885>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 3 m, Socket straight, on free cable end

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



IPD PL 5P2,5 F A5,0 PVC GY - Connecting cable

1526886

<https://www.phoenixcontact.com/in/products/1526886>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 5 m, Socket straight, on free cable end

IPD PL 5P2,5 M A0,5 F PVC GY - Connecting cable

1526887

<https://www.phoenixcontact.com/in/products/1526887>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket/pin, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 0.5 m, Male straight, on Socket straight

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



IPD PL 5P2,5 M A1,0 F PVC GY - Connecting cable

1526889

<https://www.phoenixcontact.com/in/products/1526889>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket/pin, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 1 m, Male straight, on Socket straight

IPD PL 5P2,5 M A3,0 F PVC GY - Connecting cable

1526891

<https://www.phoenixcontact.com/in/products/1526891>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket/pin, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 3 m, Male straight, on Socket straight

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



IPD PL 5P2,5 M A5,0 F PVC GY - Connecting cable

1526892

<https://www.phoenixcontact.com/in/products/1526892>



Connecting cable, product family: IPD/ Push-lock connection, number of positions: 4+PE, Socket/pin, 0.5 mm² ... 2.5 mm², 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 5 m, Male straight, on Socket straight

Accessories

SEALING PLUG 10X16 RD - Sealing plug

1400284

<https://www.phoenixcontact.com/in/products/1400284>



Sealing plug, for threads pluggable, color: red

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



SEALING PLUG 14X22 RD - Sealing plug

1400270

<https://www.phoenixcontact.com/in/products/1400270>

Sealing plug, for threads pluggable, color: red



ZBF 4:UNBEDRUCKT - Zack Marker strip, flat

0808587

<https://www.phoenixcontact.com/in/products/0808587>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm

IPD P 5P2,5 M BK - Connector

1088667


<https://www.phoenixcontact.com/in/products/1088667>



UC-TMF 4 - Marker for terminal blocks

0818166

<https://www.phoenixcontact.com/in/products/0818166>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 5.1 mm, text field width: 3.6 mm

UCT-TMF 4 - Marker for terminal blocks

0828742

<https://www.phoenixcontact.com/in/products/0828742>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 90, text field height: 4.7 mm, text field width: 3.4 mm

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



IPD PL CAP W32 WP GY - Protective cap

1088711

<https://www.phoenixcontact.com/in/products/1088711>



Protective cap, IPD, with locking element, IP66, IP68, IP69K, width: 32 mm, color: gray, for IPD P 5P2,5..., for IPD W 5P2,5..., IPD H 5P,5..., IPD Y 5P2,5

IPD SEAL W32 2XASI - Seal

1698173

<https://www.phoenixcontact.com/in/products/1698173>



Seal, for connectors, product family: IPD, black, For IPD ... 5P2,5 ..., For IPD ... 5F2,5 ...

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



IPD SEAL W32 1XASI - Seal

1698174

<https://www.phoenixcontact.com/in/products/1698174>



Seal, for connectors, product family: IPD, black, For IPD ... 5P2,5 ..., For IPD ... 5F2,5 ...

QSS 27 - Socket wrench

1670646

<https://www.phoenixcontact.com/in/products/1670646>



Allen wrench, for loosening and fastening the QUICKON union nut, WAF 27 mm

IPD P 5P2,5 M BK - Connector

1088667

<https://www.phoenixcontact.com/in/products/1088667>



SZF 1-0,6X3,5 - Screwdriver

1204517

<https://www.phoenixcontact.com/in/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

CRIMPFOX VARIO 4S - Crimping pliers

1108766

<https://www.phoenixcontact.com/in/products/1108766>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, min. cross section: 0.25 mm², max. cross section: 4 mm², compression: Square crimp, weight 401 g, black/green

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in