

ToLEDo Retro Candle Dimmable

ToLEDo RT Dim Candle 470LM B22 SL

0027290



Range Features

-

PRODUCT OVERVIEW

Lamp finish	Clear
Lamp shape	Candle
Colour temperature (K)	2700
CRI (Ra)	80
Dimmable	Yes
EAN code	5410288272900
Energy class	A++
Equivalent watt (W)	40
Cap/Base	B22
Type	ToLEDo Retro Candle Dimmable
Watt (Nominal) (W)	4.5
Light colour	Homelight
Ordering number	0027290
Efficacy (Rated) (lm/w)	104.44
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	470
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (Nominal) (h)	15000
Control gear required	No
Lamp finish	Clear
Lamp shape	Candle
Dimmable	Yes
Dry applications use only	Yes

ToLEDo Retro Candle Dimmable

ToLEDo RT Dim Candle 470LM B22 SL

0027290

EAN code	5410288272900
Energy class	A++
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	B22
Lamp mercury content (mg)	0
Type	ToLEDo Retro Candle Dimmable
No. of switching cycles before premature failure (min)	>50,000
Optimal operating condition (°C)	25
Ordering number	0027290
Product name	ToLEDo RT Dim Candle 470LM B22 SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%

Optical data

Colour temperature (K)	2700
CRI (Ra)	80
Light colour	Homelight
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	470
Luminous flux (Rated) (lm)	470
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Drive current (mA)	27
Equivalent watt (W)	40
kWh per 1000 hours burning time	5
Lamp power factor	0.8
Watt (Nominal) (W)	4.5
Efficacy (Rated) (lm/w)	104.44
Watt (Rated) (W)	4.5
Voltage (V)	220-240

ToLEDo Retro Candle Dimmable

ToLEDo RT Dim Candle 470LM B22 SL

0027290

Physical data

Max. Lamp Diameter (mm) - D	36
Lamp Length (mm) - C/L	113
Lamp dimension equal to filament lamp equivalent	Yes

TECHNICAL DRAWINGS

