



## Main

Range	New Unica
Product or component type	Central plate
Accessory / separate part category	Fixing accessory
Device presentation	Mechanism
Socket number	1
Provided equipment	Label holder
Colour tint	Anthracite (RAL 7021)

## Complementary

Connector type	RJ45
Device mounting	Flush
Fixing mode	Clip-in
Installation direction	Inclined
Number of modules	1 module
Type of footprint	S-One
Material	Thermoplastic ABS-UV stabilised: central plate
Surface finish	Painted powder coated
Depth	35 mm
Width	22.5 mm
Height	45 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

IP degree of protection	IP20
IK degree of protection	IK01

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins