

FR720 - Bizflame Work Lightweight FR Shirt

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre, 210g

Outer Carton: 24



Product information

This lightweight shirt will keep you comfortable and protected in the toughest environments with high visibility reflective tape for enhanced visibility. The shirt tail will stay tucked in during movement and all day wear. Handy features include adjustable button cuffs and flapped chest pockets.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2,F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 9 CAL/CM², ATPV 9.7 CAL/CM²)

EN 17353 Type B2

Features

- Lightweight for enhanced wearer comfort
- Protection against radiant, convective and contact heat
- Two chest pockets with button and flap closure
- Pen division on left pocket
- Button front closure
- Button cuffs for a secure and comfortable fit
- 3 pockets for ample storage
- Premium sew on flame resistant reflective tape
- Radio loops for easy clipping of a radio
- 40+ UPF rated fabric to block 98% of UV rays
- Suitable to be worn in an ATEX environment

FR720 - Bizflame Work Lightweight FR Shirt
Commodity Code: 6205200090

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/27051-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR720ORRXS	Orange	60.0	40.0	28.0	0.6110	0.0672	5036108405497	15036108890702
FR720ORRS	Orange	60.0	40.0	28.0	0.6300	0.0672	5036108405473	15036108890689
FR720ORRM	Orange	60.0	40.0	28.0	0.6490	0.0672	5036108405466	15036108890672
FR720ORRL	Orange	60.0	40.0	28.0	0.6650	0.0672	5036108405459	15036108890665
FR720ORRXL	Orange	60.0	40.0	28.0	0.6900	0.0672	5036108405480	15036108890696
FR720ORRXXL	Orange	60.0	40.0	30.0	0.7300	0.0720	5036108405503	15036108890719
FR720ORRXXXL	Orange	60.0	40.0	30.0	0.7450	0.0720	5036108405510	15036108890726