

## Technical data sheet

Article number:  
111-07000

FNT1635

<b>Product Group</b>	FastNTube
<b>Material</b>	Polyamide 6.6 recycled, high impact modified, UV-stabilised (PA66HIRUV(REC))
<b>Colour</b>	Grey RAL 7035 (RAL7035)
<b>Bundle Ø max.</b>	35 mm
<b>Bundle Ø min.</b>	16 mm
<b>Flammability</b>	UL 94 HB
<b>Halogen-free</b>	Yes
<b>Length (L)</b>	175.5 mm
<b>Min.Tensile Strength</b>	320 N
<b>Operating Temperature</b>	-40 °C to +85 °C, (+105 °C, 500 h)
<b>Package Content packed in</b>	box
<b>Pack Cont.</b>	100 pcs.
<b>Releasable Closure (Yes/No)</b>	No
<b>Toothing (Serration)</b>	Inside Serrated
<b>Variant</b>	Inside Serrated
<b>Weight/Unit</b>	0.0036 kg
<b>Width (W)</b>	7.5 mm

HF ✓

RoHS ✓