

612.20.100 -600 mbar...0 mbar 1/2 NPT lower back mount

Capsule pressure gauge, industrial series

Item number: 40038963

Quantity: 1 pcs.

Order code: 612.20-E-MAACZZ-ND-3ZZGZZZ-ZZZ V3AFZZ2FZZSAZMA
DIAL-IAZ1ZZZZZZ1Z- ZZ3Z4ZZZZ
LABEL-ASASZDE-

Overview: 612.20.100 -600 mbar...0 mbar 1/2 NPT lower back mount
Capsule pressure gauge, industrial series
class 1.6
Single packing
EN 837-3 *WIKA*
Cl.1.6

Details: Capsule pressure gauge, industrial series
Model: 612.20
Specifications according to data sheet: PM 06.02
Measuring system: copper alloy
Case: stainless steel
Movement: copper alloy
Bezel ring: cam ring (bayonet type), stainless steel
Nominal size: 100 mm
Unit: mbar
Scale range: -600 mbar...0 mbar
Process connection: 1/2 NPT
Connector location: lower back mount
Case type: without blow-out disc on top
Accuracy class: class 1.6
Movement: copper alloy
Ingress protection: IP 54
Package: Single packing
Case: stainless steel
Pointer: standard, aluminium
Pointer colour: black
Window: flat instrument glass
Dial description:
Pressure Gauge Standard: International (standard Europe)
color for 1.scale (outside): black
dial background: White
Manufacturer logo: *WIKA*
norm-mark on dial: *EN 837-3*
accuracy class on dial: *Cl.1.6*
inner packages label: Standard (with Wika Logo)
outside packages label: Standard (with Wika Logo)