

## Datasheet

### **ACCESS Series 19-Inch Cabinet, Floor Standing, 42U, 2036 x 600 x 1000mm**

RS Stock number 207-765



#### **Server Cabinets**

Supplied in flat pack form

Two fully ventilated steel doors, quick release side panels, ventilated top panels and a fully retractable stabilising plinth

Maximum static load 900 kg (uniformly distributed)

Supplied with jacking feet

Front and rear 19in mounting angles fully adjustable up to a mounting depth of 762mm between the front and rear angles