



Superior nitrile grip in oily environments. Waterproof and with chemical approval type C.

**TEGERA® OIL GRIP 8853**



[Learn more](#)

**FULLY DIPPED AND WATERPROOF**

This glove offers superior nitrile grip in oily environments. Waterproof and with chemical approval type C. Fully and triple-dipped with nitrile foam and a long cuff. The liner is knitted in 18 gg and made of over 90% recycled polyester. Additionally, the gloves feature touchscreen functionality, allowing you to handle control devices without needing to remove the gloves. Oeko-Tex approved. Withstands contact heat up to 100°C/212°F. Wide size range.

**CHARACTERISTICS**

- Durable
- Good fingertip sensitivity
- Flexible
- Comfortable
- Excellent grip in oily environments

**FUNCTIONS**

- Withstands contact heat up to 100°C
- For touchscreen
- Oil and grease resistant
- Windproof
- Waterproof
- Extra long
- Thin



**PREVENTS RISK OF**

Abrasion injuries, blisters, grazes, scratches, lacerations, chapping, contact with moisture, contact with oil and fat

**PRIMARY ENVIRONMENTS OF USE**

Wet environments, oily and greasy environments, dirty environments

**PRIMARY AREAS OF USE**

Building and construction, installation work, machine operating, mining, repair work, service work, shop work, transport work

**PRIMARY INDUSTRIES OF USE**

Agriculture, mining, oil, gas, petrochemical, machinery and equipment, mro, automotive, transportation, utilities, building and construction

**TYPE OF WORK**

Light weight

**CHEMICAL RESISTANCE**

According to EN16523-1:2015. For details, please contact Ejendals.

**SPECIFICATION**

TYPE Heat protection gloves, Precision work gloves

CATEGORY Cat. III

COLLECTION Oil Grip

LINING MATERIAL 18 gg, Recycled polyester

LENGTH 250-285 mm

DEXTERITY 5

GRIP DESIGN Foam grip pattern

COLOUR Black

PAIRS PER: BUNDLE/CARTON 6/72

DISPLAY TYPE Bulk pack

DIPPING Fully dipped, Triple-dipped

DIPPING MATERIAL Nitrile, Nitrile foam

CUFF STYLE Knitwrist cuff

CUFF MATERIAL Textile

INNER MATERIAL SPECIFICATION Recycled polyester

OUTER MATERIAL SPECIFICATION Nitrile


**COMPLIANCE**



TP TC 019:2011



EN ISO 374-1:2016/A1:2018 Type C



EN ISO 21420:2020

EN 511 cl. 4.3 Water penetration (ISO 15383): Pass



Contact heat rating valid for palm area only

Note: This product needs a few minutes of oil contact to activate the oil grip.

**FEATURES**



For touchscreen



Waterproof



Windproof

**TEST ACCORDING TO EN ISO 374-1:2016**

Tested chemical J

Permeation level 4

Degradation % 11.1

SIZE	ARTICLE NUMBER	EAN
6 XS	8853-6	7340118471662
7 S	8853-7	7340118471815
8 M	8853-8	7340118471969
9 L	8853-9	7340118472119
10 XL	8853-10	7340118472263
11 XXL	8853-11	7340118472416
12 3XL	8853-12	7340118472560

**ejendals**

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com