

## Interface module - DFLK-D50 SUB/M/FKCT - 2903058

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The VARIOFACE feed-through module implements a 1:1 connection between plug-in push-in spring-cage connection terminal blocks and a D-SUB miniature pin strip (number of positions: 50). There is no separate ground tap.



### Key commercial data

Packing unit	1 pc
GTIN	4 046356 709446
Weight per Piece (excluding packing)	146.53 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	36.5 mm
Height	143.4 mm
Depth	46 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	125 V AC/DC
Max. perm. current (per branch)	2.5 A
Max. permissible current (all branches)	50 A (at T <sub>A</sub> = 50°C)
Number of positions	50
Mounting position	any
Assembly instructions	In rows with zero spacing
Degree of protection	IP20
Standards/regulations	DIN EN 50178

# Interface module - DFLK-D50 SUB/M/FKCT - 2903058

## Technical data

### General

	IEC 60664
	IEC 62103
Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (Functional insulation)
Pollution degree	2
Surge voltage category	II

### Connection data for connection 1

Connection name	Field level
Connection method	Plug-in push-in spring-cage connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max.	12
Stripping length	10 mm

### Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB pin strip
Number of positions	50

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
-------------	----------

# Interface module - DFLK-D50 SUB/M/FKCT - 2903058

## Classifications

### UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

### Approval details

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	30-12
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

cUL Recognized	
mm <sup>2</sup> /AWG/kcmil	30-12
Nominal current I <sub>N</sub>	1 A
Nominal voltage U <sub>N</sub>	125 V

EAC
-----

cULus Recognized
------------------

## Interface module - DFLK-D50 SUB/M/FKCT - 2903058

### Accessories

#### Accessories

#### System cable

Cable - CABLE-D50SUB/B/S/ 50/KONFEK/S - 2302269



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 0.5 m

---

Cable - CABLE-D50SUB/B/S/100/KONFEK/S - 2302272



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 1 m

---

Cable - CABLE-D50SUB/B/S/150/KONFEK/S - 2302285



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 1.5 m

---

Cable - CABLE-D50SUB/B/S/200/KONFEK/S - 2302298



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 2 m

---

Cable - CABLE-D50SUB/B/S/300/KONFEK/S - 2302308



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 3 m

---

## Interface module - DFLK-D50 SUB/M/FKCT - 2903058

### Accessories

Cable - CABLE-D50SUB/B/S/400/KONFEK/S - 2302311



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 4 m

---

Cable - CABLE-D50SUB/B/S/600/KONFEK/S - 2302324



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 6 m

---

Cable - CABLE D-SUB-S/.../.../... - 2302340



Shielded round cable, assembled with one D-SUB male and one female connector, variable cable length

---

Cable - CABLE D-SUB-B-B-S/.../.../... - 2302421



Shielded round cable, assembled with two D-SUB female connectors, variable cable length

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/0,5M - 2926292



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 0.5 m.

---

## Interface module - DFLK-D50 SUB/M/FKCT - 2903058

### Accessories

Cable - CABLE-D-50SUB/F/OE/0,25/S/1,0M - 2926302



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 1 m.

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/1,5M - 2926315



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 1.5 m.

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/2,0M - 2926328



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 2 m.

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/3,0M - 2926331



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 3 m.

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/4,0M - 2926344



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 4 m.

---

# Interface module - DFLK-D50 SUB/M/FKCT - 2903058

## Accessories

Cable - CABLE-D-50SUB/F/OE/0,25/S/6,0M - 2926357



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 6 m.


Cable - CABLE-D-50SUB-F-OE-0,25-S/... - 2900908




Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: variable.

## Drawings

Dimensioned drawing



Dimensioned drawing



## Interface module - DFLK-D50 SUB/M/FKCT - 2903058

Dimensioned drawing

