

ZBFM 5/WH:UNBEDRUCKT - Flat zack marker sheet



0803595

<https://www.phoenixcontact.com/gb/products/0803595>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat zack marker sheet, Sheet, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 5.2 mm, Number of individual labels: 120, text field height: 5 mm, text field width: 4.5 mm



Commercial data

Item number	0803595
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2113
Product key	BG2113
Catalog page	Page 63 (C-6-2013)
GTIN	4017918007553
Weight per piece (including packing)	6.13 g
Weight per piece (excluding packing)	6 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Terminal marking
Pitch	5.2 mm
Type	flat

Marking

Number of individual labels	120
Number of individual labels per row	12
Number of marker strips	10

Dimensions

Width	4.55 mm
Height	6.5 mm
Depth	1.6 mm
Pitch	5.2 mm

Text field

Text field width	4.5 mm
Text field height	5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

ZBFM 5/WH:UNBEDRUCKT - Flat zack marker sheet



0803595

<https://www.phoenixcontact.com/gb/products/0803595>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

0803595

<https://www.phoenixcontact.com/gb/products/0803595>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0803595

<https://www.phoenixcontact.com/gb/products/0803595>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk