

HD16/14.FF5.20.3



Products Low Voltage Products and Systems Connection Devices Terminal Blocks Railway Terminal Blocks

General Information

Extended Product Type:	HD16/14.FF5.20.3
Product ID:	1SNA295013R1000
EAN:	3472592950136
Catalog Description:	HD16/14.FF5.20.3 - Stud terminal blocks - 2 studs M5 - Beige
Long Description:	- 2 stud terminals M5 x 19.5 mm 0.768 in, - Equipment: self locking nut + spring washer + washer, - NF F 61-017 designation: BE0014-FF5 (1SNA295013R1000).

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Beige
Connecting Capacity UL/CSA:	Stranded 6 AWG
Connecting Capacity Main Circuit:	Stud / Flexible 1x 0.5 ... 16 mm ²
Connection Type:	Stud
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC001003C0302
Declaration of Conformity - CE:	1SND225049U1000
EAC Certificate:	1SND161009A1100
EAN:	3472592950136
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220039E1002
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC001003C0302
Insulation Material:	Polyamide
Invoice Description:	HD16/14.FF5.20.3 - Stud terminal blocks - 2 studs M5 - Beige
Minimum Order Quantity:	25 piece
Mounting on DIN Rail:	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	25 piece
Package Level 1 EAN:	3472592950136
Package Level 1 Gross Weight:	0.65 kg
Package Level 1 Height:	51 mm
Package Level 1 Length:	250 mm
Package Level 1 Units:	25 piece
Package Level 1 Width:	86 mm

Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	600 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	14400 piece
Product Main Type:	HD16/14.FF5
Product Name:	Terminal Block
Product Net Depth:	36 mm
Product Net Height:	54 mm
Product Net Weight:	26 g
Product Net Width:	14 mm
Product Packing Type:	Box
Rated Cross-Section:	16 mm ²
Rated Current (I _n):	Main Circuit 71 A
RoHS Information:	1SND230014F0201
Selling Unit of Measure:	piece
Short Description:	beige Railway Terminal Blocks HD16/14.FF5
Spacing:	14 mm
Sub-Function:	2 studs M5
Tightening Torque:	acc. IEC 60947-1 2.5 N·m
Number of Potentials:	1

