

KEMET Part Number: SSHB10HS-13030
(UALSB1S1303000)

KEMET, SSHB10HS, AC Line Filters, Dual Mode, 3000 uH



Dimensions

L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	300
Weight:	10 g

General Information

Series:	SSHB10HS
Style:	Through-Hole
RoHS:	Yes
Notes:	Marking: 13 Lot No.
Miscellaneous:	Temperature Rise Maximum: 50 K

Specifications

Voltage AC:	250 VAC
Inductance:	3 mH (10 kHz)
Current:	1.3 A
Temperature Range:	-25/+130°C
DC Resistance:	250 mOhms