





Model No.	POS.1	POS.2	POS.3
5SES1	ON	NONE	ON
Term. Comm.	2-1	N/A	2-3
SCHEMATIC			

SWITCH FUNCTION

SPECIFICATIONS
CONTACT RATING:Max 0.4 VA max @ 48 VAC or DC
MECHANICAL LIFE: minimum 40,000 operations.
CONTACT RESISTANCE: 50mΩ max.
INSULATION RESISTANCE: 500MΩ at 250 VDC. (A)
DIELECTRIC STRENGTH: 500V, 50 Hz for the duration of 1 minute.
OPERATING TEMPERATURE: -20°C to 80°C.
DEGREE OF PROTECITON: IP67

MATERIALS
ACTUATOR - PBT,yellow std.
HOUSING - SPCC
CASE - PBT, Meets (UL94V-0),Washable
CONTACT/TERMINALS - Phosphor bronze gold - plated over nickel barrier.
TERMINAL SEAL - Epoxy
RoHS - 2002/95/EC



P.C. MOUNTING

	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例)： 3：2	TITLE 圖 名	Sub-Miniature Slide Switches			SIZE 圖紙	A4
1	Ⓐ	500mΩ, 1.09(.043)	500MΩ, 1.0(.039)	JAN-10-2011	TOLERANCE (公差)： 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR：± 5° FILE NAME：5SESP0005	DWG NO. 圖 號	5SES1S105M2RES			UNIT 單位	inch mm
2	Ⓑ					REV. 版 本	B	DATE 日 期	MAY - 05 - 2010	SHEET 張 數	1 of 1
3	Ⓒ					CHECKED BY 審 核	RICHARD		DRAWN BY 製 圖	IRENE	
4	Ⓓ										
5	Ⓔ										