



Mechanical characteristics

cable group
 interface dimensions acc. to assembly code

Mechanische Eigenschaften

Kabelgruppe
 Steckgesicht nach Montageanleitung

(b) G 7: KX 22A; KX 3B; RG-174/U; RG-188A/U; RG-316/U

IEC 60169-15
 C0703

Components

centre contact
 outer contact
 crimp ferrule
 insulator

Bauteile

Innenkontakt
 Außenkontakt
 Crimprohr
 Isolierung

Materials / Material

CuBe2
 CuZn39Pb3
 SF Cu w
 PTFE

Finish / Oberfläche

(c) Cu1Ni2Au1.27
 NiP-Au
 Cu1Ni5Au0.2

Environmental

RoHS compliant

Umgebung

RoHS konform

2002/95/EC (c)

c b a	19564	16.01.08	MA	1998	Datum/date	Name/name	Werkstoff/ material
	10937	30.11.99	BA	gez./drawn	13.05.	HR	
	9127	15.05.98	HR	gepr./appr.	13.05.98	BJ	Oberfläche/ finish
				Norm/stand.			
				Maßstab/scale	Benennung/title		
				5:1	SMA Straight Jack SMA-Kabelbuchse		 Telegärtner
				untol. Maße/ dim. without tolerances according to	Untert./doc.type	Zeichnungsnr./drawing no.	
					K	J01151A0051	 Maße/dimensions: mm
					Ersatz für/ replaces		Original: DIN A4