



FEATURES:

- Interfaces to Pomona’s .025” (.64mm) Square Pin Micrograbber (Model 4521), Rotating Micrograbber, (Model 5790), SMD Grabber (Model 5360) and Minigator (Model 5363).
- Ideal for jumping .025” (.64mm) Square Pins on PC Test Boards.
- Receptacle is gold plated to optimize the electrical connection.

MATERIALS:

Receptacle Body – Phosphor Bronze, Gold Plated
 Housing: Polypropylene, Color Matches Wire
 Wire: 22 AWG, 26 x 36 t.c., PVC Insulation .064” (1,63mm) O.D. Nom.
 Color per part number

RATINGS:

Operating Temperature: +50°C (+122°F)
 Operating Voltage: 45 VRMS
 Current: 3 Amperes Max.

ORDERING INFORMATION: Model 4741-XX-*

XX = Length in Inches, Standard Lengths: 6” (15,24cm), 12” (30,48cm), 24” (60,96cm), 36” (91,44cm)
 * = Color, Standard Colors: -0 Black, -2 Red

Model 5948
 Kit contains 1 each of 10 colors of 4741-6

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA