

FEATURES

- Front hinged, low profile switch
- Raised tread pattern
- Foot or palm operation
- Momentary (non-latching) action with SPDT contacts
- Supplied with 2m of cable
- Dual version - 2 N/O contacts
- Single foot switch also available in Red (RS 325-2686) Green (RS 325-2692) and Yellow (RS 251-2224)
- Operating temperature: -5°C to 40°C

RS PRO General Purpose Momentary Foot Switch - Thermoplastic Case Material, SP-CO, 3 A Contact Current, 250V Contact

RS Stock No.: 251-2224



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO foot switches which are ideal for a number of applications. The low profile switch is designed for improved user comfort and is constructed from plastic with a raised tread pattern. This range of foot pedal switches includes:

218-4245 – Momentary, Single Pole Double Throw (SPDT)

218-4267 – Momentary, Single Pole Double Throw (SPDT)

251-2224 - Momentary, Single Pole Double Throw (SPDT), Yellow cover and black base

325-2692 - Momentary, Single Pole Double Throw (SPDT), Green cover and black base

325-2686 - Momentary, Single Pole Double Throw (SPDT), Red cover and black base

325-2715 – Momentary, 2 NO

513-5145 – Momentary, 2 X SPST, medically approved

General Specifications

Contact Configuration	SP-CO
Switch Operation	Momentary
Case Material	Thermoplastic
Switch Environment	General Purpose
Contact Material	Silver
Colour	Yellow
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	2metres of black 3 core cable

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Voltage Rating (DC)	24V
Contact Current Rating	3A

Mechanical Specifications

Length	90mm
Height	27mm
Dimensions	90mm x 65mm x 27mm
Width	65mm

Operation Environment Specifications

Operating Temperature	-5°C to 40°C
-----------------------	--------------

Protection Category

IP Rating	IPX7
-----------	------

Approvals

Standards Met	2014/35/EU, EN 60950
Compliance/Certifications	EN 61058-2-1; EN 61058; EN 60601-1; EN 60950, RoHS





Outline Dimensions

