



iM2275 Medium Case



Give your gear extra space. With a deeper lid, the iM2275 is the first case in our Peli™ Storm Case™ line that gives you more vertical space to work with for your equipment. This case gives you the freedom to configure multiple 4K cameras, diagnostic circuit readers, or a drone with accessories.

- **20% Deeper Lid**
- Two Press & Pull Latches
- Double-layered, Soft-grip Handle
- Two Padlockable Hasps
- Vortex® Valve
- Powerful Hinges
- Peli's limited lifetime guarantee**
- Lightweight Strong HPX® Resin
- Watertight
- **Where applicable by law

CONFIGURATIONS

iM2275 - Standard

iM2275-X0000 - With No Foam

DIMENSIONS

Interior (L x W x D): 14.12 x 13.19" x 9.90 (35.9 x 33.5 x 25.1 cm)

Exterior (L x W x D): 15.25 x 15.50" x 10.22 (38.7 x 39.4 x 26 cm)

Lid Depth: 3.20" (8.1 cm)

Bottom Depth: 6.30" (16 cm)

Total Depth: 9.5" (24.1 cm)

Int Volume: 1.07 ft³ (0.03 m³)

MATERIALS

Body: Injection Molded HPX® high performance resin

Latch: Valox - Polybutylene Terephthalate (PBT)

Latch (Alt): Xenoy - Polyester/Polycarbonate blend

O-Ring: EPDM

Pins: Stainless Steel

Pins (Alt): Aluminum

Foam: 1.3/1.35 polyester

Purge Body: Valox - Polybutylene Terephthalate (PBT)

Purge Body (Alt): Xenoy - Polyester/Polycarbonate blend

Purge Vent: Gortex membrane

COLOURS

■ Black

WEIGHT

Weight With Foam: 10.25 lbs (4.6 kg)

Weight Empty: 8.00 lbs (3.6 kg)

Buoyancy: 68.80 lbs (31.2 kg)

TEMPERATURE

Minimum Temperature: -20°

Maximum Temperature: 140°

CERTIFICATIONS

MIL-STD-810F

ATA 300

FED-STD-101C

OTHER

Master Pack: 3

Military: yes

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com