

M18 FORCE LOGIC 6T Commercial Crimper

M18 HCCT-0C

- MILWAUKEE POWERSTATE Brushless Motor provides more power, more run-time, and longer life.
- The MILWAUKEE REDLITHIUM-ION Battery Pack is the most durable pack on the market delivering more run-time, power and longer battery life.
- REDLINK PLUS Electronic Intelligence enables advanced communication between your batteries and tools, allowing for unmatched levels of performance, protection, and productivity.

MODEL VARIANT



INCLUDES

- M18 HCCT-0 (1)
- Hard Case (1)

Categories: Electrical Installation

Range Spec



WHAT'S INCLUDED	M18 HCCT-0C
	M18 HCCT-0 (1)
	Hard Case (1)

PRODUCT SPECIFICATIONS	
Battery platform	M18 REDLITHIUM-ION
Voltage (V)	18
Max. aluminum wire capacity (mm²)	150
Weight with battery pack if applicable (kg)	3.7
Head rotation	350
Max. copper wire capacity (mm²)	300
Output force (kN)	53
PFM Adaptive Pressure Control System	Yes